



- |                                |   |
|--------------------------------|---|
| ① INTELLISLOT PORT             | ⑥ EXTERNAL BATTERY CONNECTOR                            |
| ② USB PORT                     | ⑦ 10A INPUT CIRCUIT BREAKER                             |
| ③ RS485 PORT                   | ⑧ INPUT POWER PLUG AND CABLE (C14)                      |
| ④ RS232 PORT                   | ⑨ NON-PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 10A) |
| ⑤ TERMINAL BLOCK COMMUNICATION | ⑩ PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 10A)     |

**NOTES:**

- UNIT DIMENSIONS (WxDxH): 16.9" x 18.6" x 3.3" (2U)  
(430mm) x (471mm) x (85mm)
- UNIT WEIGHT: 46.2lbs (21kg)
- SHIPPING DIMENSIONS (WxDxH): 22.4" x 24.3" x 10.3"  
(570mm) x (617mm) x (262mm)
- SHIPPING WEIGHT: 61.6lbs (28kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)  
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1	OUTLINE DRAWING LIEBERT GXT5 1500VA BRAZIL 230VAC RACK/TOWER UPS	DWG. NO. GXT5-1500IB_OD	DATE 5/12/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	
CHK BY L. JOHNSON	ECN NO.						
REF. DWG.	ORDER NO.						

FILE NAME: I:\dpgeg\GXT5\Submittals\A)\Outline Dwg\GXT5-1500IB\_OD