


- ① (1) C19 SOCKET
- ② (1) C19 SOCKET
- ③ TWO-POLE 20A BREAKER FOR #1 C19 SOCKET
- ④ TWO-POLE 20A BREAKER FOR #2 C19 SOCKET
- ⑤ TWO-POLE 15A BREAKER FOR (4) C13 SOCKET
- ⑥ (4) C13 SOCKET
- ⑦ TWO-POLE 15A PROG OUTLET MAINTENANCE BYPASS BREAKER
- ⑧ TWO-POLE 63A INPUT BREAKER

NOTES:

1. UNIT DIMENSIONS:
3.3 x 16.9 x 5.1 in (85 x 430 x 130 mm)
2. UNIT WEIGHT: 8.8 lbs (4.0 kg)
3. SHIPPING DIMENSIONS:
10.3 x 22.1 x 13.0 in (262 x 562 x 330 mm)
4. SHIPPING WEIGHT: 13.9 lbs (6.3 kg)
5. ALL WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.

SHEET NO. 1 OF 1	DRAWN BY: DARIO A.	TITLE PD5-202 - OPTIONAL POD FOR GXT5-8000/10KHVRT5UXL MODELS	DWG. NO. PD5-202	
CO. NO. -	DESIGNED BY: -		DATE (LATEST REV.) 5/24/2021	
REF DWG. -	APPROVED BY: LUKE J.		REVISION A	