



FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|--------------------------------|---|
| ① INTELLISLOT PORT | ⑥ EXTERNAL BATTERY CONNECTOR |
| ② USB PORT | ⑦ 20A INPUT CIRCUIT BREAKER |
| ③ RS485 PORT | ⑧ INPUT POWER PLUG (IEC 60906-1 20A) |
| ④ RS232 PORT | ⑨ NON-PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 20A) |
| ⑤ TERMINAL BLOCK COMMUNICATION | ⑩ PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 20A) |

NOTES:

- UNIT DIMENSIONS (WxDxH): 16.9" x 18.6" x 3.3" (2U)
(430mm) x (471mm) x (85mm)
- UNIT WEIGHT: 47.5lbs (21.6kg)
- SHIPPING DIMENSIONS (WxDxH): 22.4" x 24.3" x 10.3"
(570mm) x (617mm) x (262mm)
- SHIPPING WEIGHT: 58.7lbs (26.7kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT GXT5 2000VA BRAZIL
120VAC RACK/TOWER UPS

DWG. NO.
GXT5-2000LVB_OD

DATE
5/11/20

REV. #
0

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229



FILE NAME: I:\dpgeng\GXT5\Submittals\A\Outline Dwg\GXT5-2000LVB_OD